

TradeSelect® Single Pole, 15A 120V AC Switches and Lighting Controls

BRYANT

Features

- Hi-visibility yellow base for easy installation
- Elongated strap for easier wall box mounting
- Tough thermoplastic with ultrasonically welded cover and base
- Quiet snap action mechanism

Ordering Information

Description	UPC	Catalog Number
TradeSelect, Grounding, Push and Side Wire, 15A 120V AC, White	883778100895	RS115W

Listings

CSA Certified
UL Listed E3896

Specifications

Color	White nylon
-------	-------------

Performance

Max. Continuous Current	20 A
Max. Working Voltage	120V AC
Operating Temperature	Maximum continuous 60°C, minimum -20°C (without impact)



Links

[Installation Instructions](#)

[Media](#)

Dimensions in Inches (mm)

Bryant Electric • An affiliate of Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484
Phone (800) 323-2792 • Specifications subject to change without notice