

# TradeSelect® Single Pole, 15A 120V AC, Three Way Switches and Lighting Controls

# BRYANT

## Features

- Hi-visibility yellow base for easy installation
- Elongated strap for easier wall box mounting
- Tough thermoplastic with ultrasonically welded cover and base
- Quiet snap action mechanism

## Ordering Information

Description	UPC	Catalog Number
TradeSelect, Grounding, Push and Side Wire, 15A 120V AC, White	883778100932	RS315W

## Listings

CSA Certified  
UL Listed E3896

## Specifications

Color	White nylon
-------	-------------

## Performance

Max. Continuous Current	20 A
Max. Working Voltage	120V AC
Operating Temperature	Maximum continuous 60°C, minimum -20°C (without impact)



## Links

[Installation Instructions](#)

[Media](#)

Dimensions in Inches (mm)

Bryant Electric • An affiliate of Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484  
Phone (800) 323-2792 • Specifications subject to change without notice