

TradeSelect®

Single Pole, 600W 120V

Switches and Lighting Controls, Dimmers



- Features
- Optimum CFL and LED Control
 - Low End Adjustment for Fine Tuning
 - No Neutral Required

Ordering Information

Description	UPC	Catalog Number
TradeSelect, Slide Incandescent Dimmer, Slide to OFF, 600W 120V AC, Ivory	883778304323	RS600I

Listings


CSA Certified

Specifications

Color	Natural (white) nylon
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting

Performance

Max. Continuous Current	20 A
Max. Working Voltage	120V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current
Terminal Accommodations	#18 AWG 6 inch leads
Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C; Min. continuous: -40°C without impact



- Links
- [Customer Drawings](#)
 - [Installation Instructions](#)
 - [Media](#)