



Switches and Lighting Controls,  
Industrial Grade, Toggle Switches,  
Motor Disconnects, Three Pole,  
30A 600V AC, Side Wired Only,  
Black

By Bryant  
Catalog # 30003D

Switches and Lighting Controls, Industrial Grade, Toggle  
Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side  
Wired Only, Black



General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
OEM Brand Name	Hubbell Bryant
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Back & Side Wire
UPC	781786631533

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Bryant E-12 Catalog page](#)
- [Catalog Page - Bryant G-6 Catalog page](#)
- [Catalog Page - Bryant G-2 Catalog page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Motor Controllers and Disconnects](#)
- [Literature - General Literature - BRYANT® Wiring Devices](#)



A proud member of the Hubbell Family.