



Straight Blade Devices, Receptacles, QUADPLEX Receptacle, Surge Suppression, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant
Catalog # 1254SIA



Straight Blade Devices, Receptacles, QUADPLEX Receptacle, Surge Suppression, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory.

General

Application	Quad-Plex
Catalog Number	1254SIA
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Visual Status Indicator
Item Type	Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Commercial
Type	Four Outlet Receptacle
UPC	781786190030

Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.5 lb
Width	4.3 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-1254SIA-SPEC-EN | REV 6/2024