BRYANT®

Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black



By Bryant
Catalog # 20403

Locking Devices, Bryant Power Interrupting, Industrial, Receptacle,30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Thermoset molded housing provides maximum heat resistance

Application

Extra Heavy Duty Industrial Specification Grade

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	3-Pole

Current

Amperage Rating	20A/30 A
Voltage Rating Description	250 VDC/600 VAC
Current/Amperage Rating Description	20 Amp /30 Amp
Current Rating	20A/30 A
Voltage Rating	250 VDC/600 VAC
Connectivity	Terminal Screws
Phase	Single Phase

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Height	1.75 in
Width	1.94 in
Dimensions	3.28 in x 1.94 in x 1.75 in

General

Style	Grounding
UPC	781786618473
Type	Receptacle
Material - Mounting Hardware	Screw Mounting
Item Type	20A/30A Single Receptacle
Material	Composite

Logistics

Carton Quantity	20

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved