



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal and White

By Bryant
Catalog # 21415



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 250V DC/30A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black nylon with cord grip.

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

General

Application	Extra Heavy Duty Industrial
Catalog Number	21415
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A/20A Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Grounding
Type	Plugs
UPC	781786618619

Dimensions

Dimensions	2.33 in x 2.33 in x 5.62 in
Display Size	Standard Sized
Height	5.62 in
Length	2.33 in
Width	2.33 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Screw Terminals
Current Rating	30 A
Phase	Three Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#10 AWG to #6 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-21415-SPEC-EN | REV 6/2024