



# Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant  
Catalog # 23005

Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V AC or DC/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White.



## Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

## General

Application	Extra Heavy Duty Industrial
Catalog Number	23005
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/20A Male Nylon Non-Grounding Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Non-Grounding
Type	Plugs
UPC	781786618879

## Dimensions

Dimensions	1.62 in x 1.62 in x 3.56 in
Display Size	Standard Sized
Height	3.56 in
Length	1.62 in
Width	1.62 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Multi Phase
Voltage Rating	125 VAC/125 VDC/250 VDC/480 VDC
Voltage Rating Description	125 VAC/125 VDC/250 VDC/480 VDC
Wattage	

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-23005-SPEC-EN | REV 6/2024