



# Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow

By Bryant  
Catalog # 26419



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 60A 600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Yellow polycarbonate outer cover and adjustable cord grip.

## Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated, color coded metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with stainless steel terminal screws provide maximum termination strength and dependability

## General

Application	Extra Heavy Duty Industrial
Catalog Number	26419
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Grounding
Type	Plugs
UPC	781786584198

## Dimensions

Dimensions	3.03 in x 4.65 in x 4.65 in
Display Size	Standard Sized
Height	4.65 in
Length	3.03 in
Width	4.65 in

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current Rating	60 A
Phase	Multi Phase
Voltage Rating	600 VAC
Voltage Rating Description	600 VAC
Wattage	

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-26419-SPEC-EN | REV 6/2024