



# Switches and Lighting Controls, Industrial Grade, Toggle Switches, MotorDisconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black

By Bryant  
Catalog # 30002D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, MotorDisconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black.

## General

Catalog Number	30002D
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Open Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Standard Toggle
Style	Motor Controller/Disconnect
Type	Back & Side Wire
UPC	781786631502

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

## Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Carton Quantity	10
Pallet Quantity	2640

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-30002D-SPEC-EN | REV 6/2024