



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant
Catalog # 30303D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Three Pole, 30A 600V AC, Side Wired Only, Black, With NEMA 3R Enclosure.

Features

- Toggle
- Motor Disconnects
- Three Pole
- 30A 600V AC
- Side Wired Only

Application

Red Slide

General

Catalog Number	30303D
EU RoHS Indicator	No
Enclosure Type	NEMA 3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches

UPC 781786631588

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	4
Pallet Quantity	480

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - 30303D](#)
- [Specifications - 30303D Specification Sheet French](#)