



Disconnect Switches, 2-Pole, 30A 600V AC, In NEMA 3R Flip Lid Enclosure

By Bryant
Catalog # 30312D



Disconnect Switches, 2-Pole, 30A 600V AC, In NEMA 3R Flip Lid
Enclosure

Application

Lift Cover

General

Catalog Number	30312D
EU RoHS Indicator	No
Enclosure Type	NEMA 3/3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631595

Dimensions

Display Size

Standard Sized Product

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	4
-----------------	---

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 30312D Specification Sheet French](#)
- [Specifications - 30312D Specification Sheet English](#)



A Hubbell brand