



Disconnect Switches, 3-Pole, 30A 600V AC, In NEMA 3R Flip Lid Enclosure

By Bryant
Catalog # 30313D

Disconnect Switches, 3-Pole, 30A 600V AC, In NEMA 3R Flip Lid Enclosure.



General

Application	Lift Cover
Catalog Number	30313D
EU RoHS Indicator	No
Enclosure Type	NEMA 3/3R
Environmental Conditions	Indoor and Outdoor
Item Type	Enclosed Switch
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3 Pole
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Minimum Continuous -40 Deg C without Impact
Series	Non-Fused
Style	Standard Duty
Type	Disconnect Switches
UPC	781786631601

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Three Phase
Voltage Rating	600V AC kV
Voltage Rating Description	600V AC kV
Wattage	18000

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand