



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 100-130V, Watertight

By Bryant
Catalog # 332R4W



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 32A 100-130V, 2-Pole 3-Wire Grounding, Terminal Screw, Yellow, Watertight.

General

Application	High Ampacity Connections
Catalog Number	332R4W
Color	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Watertight - IP67
Type	Receptacle
UPC	781786250550

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	32 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	32 A
Current Rating	32 A
Phase	Single Phase
Voltage Rating	100-130 V
Voltage Rating Description	100-130V
Wattage	4160

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets



A Hubbell brand