



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 100A 125/250V, Screw Terminals, Watertight



By Bryant  
Catalog # 4100C12W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 100A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Orange, Watertight.

### General

Application	High Ampacity Connections
Catalog Number	4100C12W
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector
UPC	781786250772

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Voltage Rating	125 VAC 250 VAC
Voltage Rating Description	125/250V AC

### Conductor Related

Conductor Range	#3 AWG to #1/0 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding

### Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

### Product Assets



A Hubbell brand