



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Watertight



By Bryant  
Catalog # 420P12W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male Plug, 20A 125/250V, 3-Pole 4-Wire Grounding, Screw Terminals, Orange, Watertight.

## General

Application	High Ampacity Connections
Catalog Number	420P12W
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	Watertight - IP67
Type	Plugs
UPC	781786251052

## Dimensions

Display Size	Standard Sized
--------------	----------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC 250 VAC
Voltage Rating Description	125 VAC;250 VAC
Wattage	2500

## Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Product Assets



A Hubbell brand