

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 30A 3-Phase Delta 250V AC, Screw Terminals, Watertight

Par Bryant

No de catalogue [430R9W](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Receptacle, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Screw Terminals, Blue, Watertight.

Général

Numéro de catalogue	430R9W
Couleur	Bleu
Indicateur RoHS de l'UE	Oui
Conditions environnementales	Étanchéité
Type d'article	A simple bride
Matériau	Composite
Matériau - Matériel de montage	Montage par vis
Nombre de pôles	3 pôles
Série	Étanchéité - IP67
Type	Réceptacle
CUP	781786251281

Dimensions

Taille de l'affichage	Produit de taille standard
-----------------------	----------------------------

Caractéristiques électriques

Intensité nominale	30 A
Connectivité	Vis du terminal de pression
Courant / Intensité nominale	30 A
Valeur nominale actuelle	30 A
Phase	Triphasé
Tension Rating	3 Phase 250 V
Tension nominale Description	3 phases 250V
Puissance	7500

Chef d'orchestre

Nombre de fils	4 fils
Wire Size	#12 AWG à #8 AWG

Certifications et conformité

Nema Rating	Non-NEMA
Normes - Conformité à la directive RoHS	CM

Documentation

[Spécifications - 430R9W](#)

[Spécifications - 430R9W](#)