



Locking Devices, Locking Devices, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black and White

By Bryant
Catalog # 4730



Locking Devices, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Black and White.

General

Application	Heavy Duty Industrial
Catalog Number	4730
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Regular Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Style	Two-Piece Cord Clamp
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786656628

Dimensions

Dimensions	1.53 in x 1.53 in x 2.78 in
Display Size	Standard Sized Product
Height	2.78 in
Length	1.53 in
Width	1.53 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Nema Rating	L5-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-4730-SPEC-EN | REV 6/2024