



Locking Devices, Locking Devices,
Industrial, Flush Receptacle, 15A
277V AC, 2-Pole 3-Wire Grounding,
L7-15R, Screw Terminal, Black, With
Cover

By Bryant
Catalog # 4761

Locking Devices, Industrial, Flush Receptacle, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15R, Screw Terminal, Black, Mounted on 4" Round Metal Box

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	4761
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Nylon Single Receptacle-Mounted on 4" Round Metal Box
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Style	Box Mounted
Type	Receptacle
UPC	781786623330

Dimensions



Display SizeStandard Sized Product

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L7-15R
-------------	--------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 4761 Specification Sheet English](#)
[Specifications - 4761 Specification Sheet French](#)



A Hubbell brand