



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 100A 3-Phase Wye 120/208V AC, Watertight



By Bryant  
Catalog # 5100C9W

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female Connector Body, 100A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Screw Terminals, Blue, Watertight.

### General

Application	High Ampacity Connections
Catalog Number	5100C9W
Color	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Watertight
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	4-Pole
Series	Watertight - IP67
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector
UPC	781786251601

### Dimensions

Display Size	Standard Sized Product
--------------	------------------------

### Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Voltage Rating	3 Phase Y 120/208 V
Voltage Rating Description	3 Phase Y 120/208V

### Conductor Related

Conductor Range	#3 AWG to #1/0 AWG
Number Of Wires	5-Wire
Number of Conductors	5-Wire Grounding

### Certifications And Compliance

Nema Rating	Non-NEMA
Standards - RoHS Compliance	CM
Status	

### Product Assets



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-5100C9W-SPEC-EN | REV 6/2024