



# Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, Isolated Ground, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray, Single Pack

By Bryant  
Catalog # 5261IGGRY



Straight Blade Devices, Receptacles, Single,  
Commercial/Industrial Grade, Isolated Ground, 2-Pole 3-Wire  
Grounding, 15A 125V, 5-15R, Gray, Single Pack.

## General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	5261IGGRY
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786714021

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.1 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-5261IGGRY-SPEC-EN | REV 6/2024