



# Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Isolated Ground, 20A 125V, 5-20R, Single Pack

By Bryant  
Catalog # 5361IG



Straight Blade Devices, Receptacles, Single, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Isolated Ground, 20A 125V, 5-20R, Orange, Single Pack.

## General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	5361IG
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786625488

## Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.1 lb
Width	1.38 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-5361IG-SPEC-EN | REV 6/2024