



Straight Blade Devices,  
Receptacles, Single,  
Commercial/Industrial Grade, 2-  
Pole 3-Wire Grounding, Isolated  
Ground, 20A 125V, 5-20R, Single  
Pack

By Bryant  
Catalog # 5361IGW



Straight Blade Devices, Receptacles, Single,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, Isolated  
Ground, 20A 125V, 5-20R, White, Single Pack

Features

- Single
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- Isolated Ground
- 20A 125V

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5361IGW
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786625563

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in

Length	3.28 in
Weight	0.1 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 5361IGW Specification Sheet English](#)  
[Specifications - 5361IGW Specification Sheet French](#)



A Hubbell brand