



Straight Blade Devices, Receptacles, Single, Weather Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R

By Bryant
Catalog # 5361IWR



Straight Blade Devices, Receptacles, Single, Weather Resistant, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Ivory, Single Pack.

General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	5361IWR
Color	
EU RoHS Indicator	No
Environmental Conditions	Weather Resistant
Item Type	Single
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Extra Heavy Duty
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786670747

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in
Length	3.28 in
Weight	0.15 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-53611WR-SPEC-EN | REV 6/2024