



Straight Blade Devices,
Receptacles, Duplex,
Commercial/Industrial Grade, 2-
Pole 3-Wire Grounding, 15A 277V
AC, 7- 15R, Brown, Single Pack

By Bryant
Catalog # 5762



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
277V AC, 7- 15R, Brown, Single Pack

Features

- Duplex
- Commercial/Industrial Grade
- 2-Pole 3-Wire Grounding
- 15A 277V AC
- 7- 15R

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	5762
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786664401

Dimensions

Dimensions	3.28 in x 1.38 in x 0.86 in
Display Size	Standard Sized Product
Height	0.86 in
Length	3.28 in

Weight	0.2 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	277 V
Voltage Rating Description	277 V
Wattage	4155

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	7-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 5762 Specification Sheet French](#)
[Specifications - 5762 Specification Sheet English](#)



A Hubbell brand