



# Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Side Wired Only, With NEMA 3R Enclosure

By Bryant  
Catalog # 60302D



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Manual Motor Controllers, Double Pole, 60A 600V AC, Side Wired Only, Black, With NEMA 3R Enclosure.

## General

|                              |   |
|------------------------------|---|
| Application                  | Red Slide                                   |
| Catalog Number               | 60302D                                      |
| EU RoHS Indicator            | No  |
| Enclosure Type               | NEMA 3R                                     |
| Environmental Conditions     | Indoor and Outdoor                          |
| Item Type                    | Enclosed Switch                             |
| Load Capacity                | Inductive                                   |
| Material - Mounting Hardware | Screw Mounting                              |
| Number Of Poles              | 2 Pole                                      |
| Operating Cycles             | 10,000 Cycles Minimum                       |
| Operating Temperature        | Minimum Continuous -40 Deg C without Impact |
| Series                       | Non-Fused                                   |
| Style                        | Standard Duty                               |
| Type                         | Disconnect Switches                         |
| UPC                          | 781786631779                                |

## Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

## Electrical Ratings

|                            |                          |
|----------------------------|--------------------------|
| Amperage Rating            | 60 A                     |
| Connectivity               | Pressure Terminal Screws |
| Current / Amperage Rating  | 60 A                     |
| Current Rating             | 60 A                     |
| Phase                      | Single Phase             |
| Voltage Rating             | 600V AC kV               |
| Voltage Rating Description | 600V AC kV               |
| Wattage                    | 36000                    |

## Certifications And Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 4 |
|-----------------|---|

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-60302D-SPEC-EN | REV 6/2024