



# Locking Devices, Isolated Ground Industrial, Duplex Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Orange

By Bryant  
Catalog # 70615DRIG



Locking Devices, Isolated Ground Industrial, Duplex Receptacle, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Orange.

### Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- Single point break-off tabs
- Mounting strap tabs lock the body and base together

### General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	70615DRIG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	15A Duplex Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Locking
Style	Isolated Ground
Type	Duplex Receptacle
UPC	781786616318

### Dimensions

Dimensions	3.28 in x 1.70 in x 1.17 in
Display Size	Standard Sized Product
Height	1.17 in
Length	3.28 in
Width	1.7 in

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

### Certifications And Compliance

Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-70615DRIG-SPEC-EN | REV 6/2024