



# Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Orange

By Bryant  
Catalog # [71430IG](#)



Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Orange.

## General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	71430IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786695344

## Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250V AC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L14-30R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-71430IG-SPEC-EN | REV 6/2024