



Locking Devices, Industrial,
Receptacle, 50A 250V DC/600V
AC, 3-Pole 4-Wire Grounding, Non-
NEMA, Screw Terminal, Black

By Bryant
Catalog # 7379



Locking Devices, Industrial, Receptacle, 50A 250V DC/600V AC,
3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- 50A 250V DC/600V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	7379
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Single Armored Heavy Duty Receptacle-For Replacement Use
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Extra Heavy Duty
Type	Receptacle
UPC	781786668508

Dimensions

Dimensions	3.28 in x 2.12 in x 2.44 in
Display Size	Standard Sized Product
Height	2.44 in
Length	3.28 in
Width	2.12 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Terminal Screws
Current Rating	50 A
Phase	Single Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 7379 Specification Sheet French](#)
[Specifications - 7379 Specification Sheet English](#)



A Hubbell brand