



# Locking Devices, Industrial, Male Plug, 15A 125V/10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # 7568NP



Locking Devices, Industrial, Male Plug, 10A 250V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black.

## Features

- Hand grip features wide-rib, non-slip design
- Configuration-specific plug face surrounds blades to prevent infiltration of contaminants
- Captive, combination Slot/Phillips assembly screws
- Double wall construction for extra durability
- Neutral blade is nickel-plated for easy identification
- Internal “self-centering” Triple Gripper® cord grip with “radius teeth” design provides secure cord retention

## General

Application	Extra Heavy Duty Industrial
Catalog Number	7568NP
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A Triple Gripper Nylon Plug Non-NEMA
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Internal Cord Clamp
Type	Plugs
UPC	781786010451

## Dimensions

Dimensions	1.53 in x 1.53 in x 2.18 in
Display Size	Standard Sized
Height	2.18 in
Length	1.53 in
Width	1.53 in

## Electrical Ratings

Amperage Rating	10 A
Connectivity	Screw Terminals
Current Rating	10 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-7568NP-SPEC-EN | REV 6/2024