



**Straight Blade Devices,  
Receptacles, Single, Hospital Grade,  
15A 125V, 2-Pole 3-Wire Grounding,  
Back and Side Wired, 5-15R,  
Orange, Single Pack**

By Bryant  
Catalog # [8210IG](#)

Straight Blade Devices, Receptacles, Single, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-15R, Orange, Single Pack

**Features**

- Single
- Hospital Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- Back and Side Wired

**Application**

Hospital Grade

**General**

Catalog Number	8210IG
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786731349

**Dimensions**

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in



Length	3.28 in
Weight	0.1 lb
Width	1.38 in

**Electrical Ratings**

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

**Conductor Related**

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

**Certifications And Compliance**

Nema Rating	5-15R
-------------	-------

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 8210IG Specification Sheet English](#)  
[Specifications - 8210IG Specification Sheet French](#)



A Hubbell brand