



**Straight Blade Devices,
Receptacles, Single, Hospital Grade,
20A 125V, 2-Pole 3-Wire Grounding,
Back and Side Wired, 5-20R,
Orange, Single Pack**

By Bryant
Catalog # 8310IG

Straight Blade Devices, Receptacles, Single, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-20R, Orange, Single Pack

Features

- Single
- Hospital Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- Back and Side Wired

Application

Hospital Grade

General

Catalog Number	8310IG
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Finder Groove Face
Type	Single Receptacle
UPC	781786731356

Dimensions

Dimensions	3.28 in x 1.38 in x 0.91 in
Display Size	Standard Sized Product
Height	0.91 in



Length	3.28 in
Weight	0.1 lb
Width	1.38 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 8310IG Specification Sheet English](#)
- [Specifications - 8310IG Specification Sheet French](#)



A Hubbell brand