



# Straight Blade Devices, Receptacles, Single, Hospital Grade, 20A 250V, 2-Pole 3-Wire Grounding, Back and Side Wired, 6-20R, Orange, Single Pack

By Bryant  
Catalog # 8410IG



Straight Blade Devices, Receptacles, Single, Hospital Grade, 20A 250V, 2-Pole 3-Wire Grounding, Back and Side Wired, 6-20R, Orange, Single Pack.

## General

|                              |   |
|------------------------------|---|
| Application                  | Hospital Grade                                  |
| Catalog Number               | 8410IG  |
| Color                        |   |
| EU RoHS Indicator            | No  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Item Type                    | Single  |
| Material                     | Composite                                       |
| Material - Mounting Hardware | Screw Mounting                                  |
| Number Of Poles              | 2-Pole  |
| Series                       | Hospital Grade                                  |
| Style                        | Finder Groove Face                              |
| Type                         | Single Receptacle                               |
| UPC                          | 781786731431                                    |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 3.28 in x 1.38 in x 0.91 in |
| Display Size | Standard Sized Product      |
| Height       | 0.91 in                     |
| Length       | 3.28 in                     |
| Weight       | 0.15 lb                     |
| Width        | 1.38 in                     |

## Electrical Ratings

|                            |                     |
|----------------------------|---------------------|
| Amperage Rating            | 20 A                |
| Connectivity               | Back and Side Wired |
| Current / Amperage Rating  | 20 A                |
| Current Rating             | 20 A                |
| Phase                      | Single Phase        |
| Voltage Rating             | 250 V               |
| Voltage Rating Description | 250 V               |
| Wattage                    | 5000                |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |

## Certifications And Compliance

|             |       |
|-------------|-------|
| Nema Rating | 6-20R |
|-------------|-------|

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-8410IG-SPEC-EN | REV 6/2024