



Straight Blade Devices,
Receptacles, Duplex, Decorator
Hospital Grade, Isolated Ground,
Back and Side Wired, 15A 125V, 2-
Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # 9200IGRED



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital
Grade, Isolated Ground, Back and Side Wired, 15A 125V, 2-Pole 3-
Wire Grounding, 5-15R, Red, Single Pack

Features

- Duplex
- Decorator Hospital Grade
- Isolated Ground
- Back and Side Wired
- 15A 125V

Application

Hospital Grade

General

Catalog Number	9200IGRED
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Decorator
Type	Single Receptacle
UPC	781786741690

Dimensions

Dimensions	3.28 in x 1.36 in x 1.03 in
Display Size	Standard Sized Product
Height	1.03 in

Length	3.28 in
Weight	0.25 lb
Width	1.36 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 9200IGRED Specification Sheet English](#)
[Specifications - 9200IGRED Specification Sheet French](#)



A Hubbell brand