



**Straight Blade Devices,
Receptacles, Duplex, Decorator
Hospital Grade, Isolated Ground,
20A 125V, 2-Pole 3-Wire Grounding,
Back and Side Wired, 5-20R**

By Bryant
Catalog # 9300IGGRY



Straight Blade Devices, Receptacles, Duplex, Decorator Hospital Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, Back and Side Wired, 5-20R, Gray, Single Pack.

General

Application	Hospital Grade
Catalog Number	9300IGGRY
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Straight Blade
Style	Decorator
Type	Single Receptacle
UPC	781786741812

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-9300IGGRY-SPEC-EN | REV 6/2024