



**Straight Blade Devices, Male Plug,
Heavy Duty, Industrial/Commercial
Grade, Angled, 50A 250V, 2-Pole 3-
Wire Grounding, 6-50P, Black,
Single Pack**

By Bryant
Catalog # [9650ANPB](#)

Engineered specifically for EV charging applications, Hubbell's 14-50P straight blade angled plug stands out as a superior and reliable choice, fully compatible with established EV charging standards. This sturdy plug is crafted to offer exceptional durability, safety, and high performance, making it the ideal choice for environments that demand reliability in EV power delivery.



Features

- **Material & Construction:** Made from industrial-grade nylon, this plug stands up to the rigorous demands of daily use. Its superior build ensures longevity and consistent performance, which is critical for maintaining the operational integrity of EV charging systems.
- **Configuration:** Features a 4-position, angled configuration with 3 poles and 4 wires, including a grounding wire. This setup not only supports the high electrical demands typical of EV charging but also significantly enhances safety by preventing electrical hazards.
- **Electrical Rating:** Boasting a 50A, 125/250V capacity, this plug is suited for high-powered EV charging stations, ensuring efficient and reliable power delivery.
- **Safety Compliance:** Adhering to rigorous safety standards, this plug incorporates a grounding pin and is constructed with heavy-duty materials to minimize the risk of electrical shocks, ensuring a secure connection that protects both the charging equipment and users.
- **Ease of Use:** Designed with an angled interface, the plug allows for straightforward access and operation, even in confined spaces typical at charging stations. The ergonomic handle design provides extra leverage, facilitating easy and safe insertion and removal.
- **Long-Term Reliability:** Investing in Hubbell's Straight Blade Male Plug means choosing a product that will not only meet the current demands of EV charging but also continue to deliver performance and safety long into the future.

General

Application	Heavy Duty
Catalog Number	9650ANPB
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Standard
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Heavy Duty
Type	Plug
UPC	781786677425

Dimensions

Display Size	Standard Sized
Length	4.13 in
Weight	0.9 lb
Width	2.88 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	12500

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#6 AWG

Certifications And Compliance

Nema Rating	6-50P
-------------	-------

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-9650ANPB-SPEC-EN | REV 6/2024