



# Locking Devices, Locking Devices, Industrial, Male Plug, 20A 125/250V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal, Black

By Bryant  
Catalog # 9965NB



Locking Devices, Industrial, Male Nylon Plug, 20A 125/250V AC, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black.

## General

Application	Extra Heavy Duty Industrial
Catalog Number	9965NB
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Nylon Plug-For Replacement Use
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Internal Cord Clamp
Type	Plugs
UPC	781786616868

## Dimensions

Dimensions	2.11 in x 2.11 in x 2.60 in
Display Size	Standard Sized
Height	2.6 in
Length	2.11 in
Width	2.11 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC
Wattage	

## Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-9965NB-SPEC-EN | REV 6/2024