



# Straight Blade Devices, Male Plug, Corrosion Resistant, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3- Wire Grounding, 5-15P, Single Pack

By Bryant  
Catalog # BRY5266NPCR



Straight Blade Devices, Male Plug, Corrosion Resistant, Industrial/Commercial Grade, Straight, 15A 125V, 2-Pole 3- Wire Grounding, 5-15P, Yellow ,Single Pack.

## General

Application	Extra Heavy Duty Industrial Grade
Catalog Number	BRY5266NPCR
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Extra Heavy Duty
Type	Plug
UPC	781786134041

## Dimensions

Dimensions	2.18 in x 1.52 in x 1.38 in
Display Size	Standard Sized
Height	1.38 in
Length	2.18 in
Weight	0.1 lb
Width	1.52 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

## Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-15P
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	10
Pallet Quantity	4500

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-BRY5266NPCR-SPEC-EN | REV 6/2024