



# Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Black, Single Pack

By Bryant  
Catalog # [BRY5366NP](#)



Straight Blade Devices, Male Plug, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3-Wire Grounding, 5-20P, Black, Single Pack.

## General

|                              |   |
|------------------------------|---|
| Application                  | Extra Heavy Duty Industrial Grade               |
| Catalog Number               | BRY5366NP                                       |
| Color                        | Black and White                                 |
| Cord Range                   | 0.300"-0.655"                                   |
| EU RoHS Indicator            | Yes   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Item Type                    | Tech-Spec Triple Gripper                        |
| Material                     | Composite                                       |
| Material - Mounting Hardware | Cord Mounted                                    |
| Number Of Poles              | 2-Pole  |
| Series                       | Industrial                                      |
| Style                        | Extra Heavy Duty                                |
| Type                         | Plug  |
| UPC                          | 781786005884                                    |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 2.18 in x 1.52 in x 1.38 in |
| Display Size | Standard Sized              |
| Height       | 1.38 in                     |
| Length       | 2.18 in                     |
| Weight       | 0.15 lb                     |
| Width        | 1.52 in                     |

## Electrical Ratings

|                            |                 |
|----------------------------|-----------------|
| Amperage Rating            | 20 A            |
| Connectivity               | Screw Terminals |
| Current / Amperage Rating  | 20 A            |
| Current Rating             | 20 A            |
| Phase                      | Single Phase    |
| Voltage Rating             | 125 V           |
| Voltage Rating Description | 125 V           |
| Wattage                    | 2500            |

## Conductor Related

|                 |                    |
|-----------------|--------------------|
| Cord Type       | All Portable       |
| Number Of Wires | 3-Wire             |
| Wire Size       | #14 AWG to #12 AWG |

## Certifications And Compliance

|                                    |       |
|------------------------------------|-------|
| Nema Rating                        | 5-20P |
| Standards - RoHS Compliance Status | CM    |

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 5400 |

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-BRY5366NP-SPEC-EN | REV 6/2024