



**Straight Blade Device, Male Plug,
Corrosion Resistant,
Industrial/Commercial Grade,
Straight, 20A 125V, 5-20P,
Corrosion Resistant**



By Bryant
Catalog # BRY5366NPCR

Straight Blade Devices, Male Plug, Corrosion Resistant,
Industrial/Commercial Grade, Straight, 20A 125V, 2-Pole 3- Wire
Grounding, 5-20P, Yellow, Single Pack, Corrosion Resistant.

General

Application	Extra Heavy Duty Industrial Grade
Catalog Number	BRY5366NPCR
Color	
Cord Range	0.245"-0.655"
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Extra Heavy Duty
Type	Plug
UPC	781786134126

Dimensions

Dimensions	2.18 in x 1.52 in x 1.38 in
Display Size	Standard Sized
Height	1.38 in
Length	2.18 in
Weight	0.1 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-BRY5366NPCR-SPEC-EN | REV 6/2024