



Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 250V, 2-Pole 3- Wire Grounding, 6-20R, Yellow, Hi-Viz Yellow

By Bryant
Catalog # BRY5469NCSY



Straight Blade Devices, Female Connector Body, Heavy Duty, Industrial/Commercial Grade, Straight, 20A 250V, 2-Pole 3- Wire Grounding, 6-20R, Yellow, Single Pack, Hi-Viz Yellow.

General

Application	Extra Heavy Duty Industrial Grade
Catalog Number	BRY5469NCSY
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Tech-Spec Triple Gripper
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	Industrial
Style	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786134171

Dimensions

Dimensions	2.95 in x 1.52 in x 1.38 in
Display Size	Standard Sized Product
Height	1.38 in
Length	2.95 in
Weight	0.1 lb
Width	1.52 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	6-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-BRY5469NCSY-SPEC-EN | REV 6/2024