



**Straight Blade Devices,  
Receptacles, Duplex,  
Commercial/Industrial Grade, 20A  
125V and 250V, 2-Pole 3-Wire  
Grounding, 5-20R and 6- 20R,  
Brown**

By Bryant  
Catalog # [BRY5492](#)



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 20A 125V and 250V, 2-Pole 3-Wire  
Grounding, 5-20R and 6- 20R, Brown, Single Pack.

**General**

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	BRY5492
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Finder Groove Face
Type	Combination Receptacle
UPC	781786005433

**Dimensions**

Dimensions	3.28 in x 1.54 in x 1.16 in
Display Size	Standard Sized Product
Height	1.16 in
Length	3.28 in
Weight	0.25 lb
Width	1.54 in

**Electrical Ratings**

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	5000

**Conductor Related**

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

**Certifications And Compliance**

Nema Rating	5-20R, 6-20R
Standards - RoHS Compliance Status	CM

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-BRY5492-SPEC-EN | REV 6/2024