



Straight Blade Devices, Receptacles, Tamper- Resistant Duplex, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown, Single Pack

By Bryant
Catalog # BRY8200TR



Straight Blade Devices, Receptacles, Tamper- Resistant Duplex, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5- 15R, Brown, Single Pack.

General

Application	Hospital Grade
Catalog Number	BRY8200TR
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Hospital Grade
Style	Finder Groove Face
Type	Duplex Receptacle
UPC	781786005754

Dimensions

Dimensions	3.28 in x 1.65 in x 2.75 in
Display Size	Standard Sized Product
Height	2.75 in
Length	3.28 in
Weight	0.3 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY_CA-BRY8200TR-SPEC-EN | REV 6/2024