



Straight Blade Devices,
Receptacles, Duplex, Tamper-
Resistant Commercial Grade, 15A
125V, 2- Pole 3-Wire Grounding, 5-
15R, Black, Single Pack

By Bryant
Catalog # [CBRS15BLKTR](#)



Straight Blade Devices, Receptacles, Duplex, Tamper-Resistant
Commercial Grade, 15A 125V,2- Pole 3-Wire Grounding, 5-15R,
Black, Single Pack

Features

- Duplex
- Tamper-Resistant Commercial Grade
- 15A 125V
- 2- Pole 3-Wire Grounding
- 5-15R

Application

Commercial Specification Grade

General

Catalog Number	CBRS15BLKTR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Commercial
Style	Smooth Face
Type	Duplex Receptacle
UPC	781786410626

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Weight	0.15 lb
--------	---------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - CBRS15BLKTR Specification Sheet French](#)
[Specifications - CBRS15BLKTR Specification Sheet English](#)



A Hubbell brand