



Locking Devices, Locking Devices,
Economy, Flanged Inlet, 50A
125/250, 3-Pole 4-Wire Grounding,
Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS6375L](#)

Locking Devices, Economy, Flanged Inlet, 50A 125/250V, 3-Pole
4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Application

Extra Heavy Duty Industrial

General

Catalog Number	CS6375L
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	50A Male Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Replacement Part
Style	Heavy Duty
Type	Locking Inlet
UPC	783585320717

Dimensions

Display Size	Standard Sized Product
Length	2.7 in



Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	30
-----------------	----

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - CS6375L](#)
- [Specifications - CS6375L Specification Sheet French](#)
- [Specifications - CS6375L Specification Sheet English](#)



A Hubbell brand