



Locking Devices, Twist-Lock®, Economy, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

By Bryant
Catalog # [CS8364L](#)

Locking Devices, Economy, Female Connector Body, 50A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black

Features

- Female Connector Body
- 50A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- Non-NEMA
- Screw Terminal

Application

Heavy Duty Industrial

General

Catalog Number	CS8364L
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	50A Nylon Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Style	Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	783585320731

Dimensions

Dimensions	5.50 in x 2.40 in x 2.40 in
Display Size	Standard



Height	2.4 in
Length	5.5 in
Width	2.4 in

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current Rating	50 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Conductor Range	#6 AWG
Number Of Wires	4-Wire
Number of Conductors	4-Wire Grounding
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Carton Quantity	30
Pallet Quantity	1620

Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - CS8364L](#)
- [Specifications - CS8364L Specification Sheet English](#)
- [Specifications - CS8364L Specification Sheet French](#)



A Hubbell brand