



## Lampholders, Fluorescent Starter, 14-15-20W

By Bryant  
Catalog # FS2A

Lampholders, Fluorescent Starter, 14-15-20W.



### General

Application	Low Wattage Fluorescent
Catalog Number	FS2A
Color	
EU RoHS Indicator	No
Item Type	Fluorescent Starters
Lamp Type	Pre-Heat
Material - Mounting Hardware	Plug-In
Minimum Starting Temperature	40 Degrees F °
Series	Fluorescent Starters
Start Type	Neo-Start
Type	Neostart
UPC	781786689701

### Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120/277V AC kV
Wattage	14, 15, 20W

### Logistics

Carton Quantity	25
-----------------	----

### Product Assets

[Catalogs - Bryant Full Line Catalog](#)