



Lampholders, Fluorescent Starter, 13-30-40W

By Bryant
Catalog # FS4A

Lampholders, Fluorescent Starter, 13-30-40W.



General

Application	Low Wattage Fluorescent
Catalog Number	FS4A
Color	
EU RoHS Indicator	No
Item Type	Fluorescent Starters
Lamp Type	Pre-Heat
Material - Mounting Hardware	Plug-In
Minimum Starting Temperature	40 Degrees F °
Series	Fluorescent Starters
Start Type	Neo-Start
Type	Neostart
UPC	781786689725

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120/277V AC kV
Wattage	13, 30, 40W

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)