



# Locking Devices, Industrial, Flush Receptacle, 30A 3-Phase 120V AC, 400Hz, 3-Pole 4-Wire Grounding, FSL3R, Screw Terminal, Black

By Bryant  
Catalog # [FSL3FR](#)

## Features

- 
- 
- 
- 
- 

## Application

Extra Heavy Duty Industrial Specification Grade

## General

Catalog Number	FSL3FR
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	30A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Single Receptacle
Type	Receptacle
UPC	781786638280

## Dimensions

Dimensions	3.28 in x 1.71 in x 1.14 in
Display Size	Standard Sized Product



Height	1.14 in
Length	3.28 in
Width	1.71 in

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Terminal Screws
Current Rating	30 A
Phase	Single Phase
Voltage Rating	3 Phase Delta 120 V
Voltage Rating Description	3 Phase Delta 120V

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#14 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	FSL3-R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - FSL3FR Specification Sheet English](#)
- [Specifications - FSL3FR Specification Sheet French](#)



A Hubbell brand