



Power Protection Products, GFCI
Circuit Breaker Sensing Modules,
Industrial, Auto Set, 120V AC, GFCI
Circuit Breakers, 4-6 mA Trip Level,
Black

By Bryant
Catalog # [GFMD120A](#)

Power Protection Products, GFCI Circuit Breaker Sensing
Modules, Industrial, Auto Set, 120V AC, GFCI Circuit Breakers, 4-
6 mA Trip Level, Black

Features

- Industrial
- Auto Set
- 120V AC
- GFCI Circuit Breakers
- 4-6 mA Trip Level

Application

Heavy Duty Industrial Commercial

General

Catalog Number	GFMD120A
Color	Black
EU RoHS Indicator	No
Enclosure Type	Toggle
Environmental Conditions	NEMA 4X with Supplied Gasket
Item Type	Auto Set Sensing Module
Material	Composite
Number Of Poles	None
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Industrial
Type	Auto Reset
UPC	781786450004

Dimensions

Dimensions	4.6 in x 2.8 in x 3.3 in
Height	3.3 in
Length	4.6 in
Width	2.8 in

Electrical Ratings

Amperage Rating	1-50 A
Connectivity	None
Current / Amperage Rating	1-50 A
Frequency Rating	80% of Full Rating Continuous
Phase	60Hz
Trip Range	.025 Seconds in
Trip Type	Standard
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Wire Size	Terminal Screws
-----------	-----------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Specifications - GFMD120A Specification Sheet French](#)
[Specifications - GFMD120A Specification Sheet English](#)



A Hubbell brand